











## Modal-Vibration Test Systems from 100 N to 2.7 kN

These exciters are specifically designed for **modal and structure analysis**. Modal shakers up to 400 N are excited by permanent magnets, with **lightweight** rare-earth magnets provided for mobile use. These shakers are characterized by **high cross-axial stiffness**. From 1000 N onwards, modal systems permit a max. displacement of 45 mm due to **TMC control**. TMC is an **electronic armature position control system** for precisely coupling the modal shaker to the specimen. The armature datum adjustment allows the operator to offset the nominal position of the armature in relation to the body. The axial stiffness can also be adjusted electronically.

A standard feature on all modal shakers is a trunnion mount. This allows a great variety of coupling options.

The Modal systems TV 51120-MNC and TV 51130-MSC are a special development of TIRA to increase the mobility. The 200 N shaker does not require an additional cooling unit and the 350 N shaker has an integrated cooling blower.



Modal shaker S 51120-M

Modal shaker S 51130-MSC

| System   | TV 51110-M     | TV 51120-M | TV 51120-MNC | TV 51130-MSC       |
|--|----------------|------------|--------------|--------------------|
| Shaker   | S 51110-M      | S 51120-M  | S 51120-MNC  | S 51130-MSC        |
| Amplifier  | BAA 120/DA 200 | BAA 500    | BAA 500      | BAA 500-MSC        |
| Blower   | -              | TB 0080    | -            | internal           |
| Rated peak force (N) Sine <sub>pk</sub> /Random <sub>RMS</sub> | 100/70         | 200/140    | 200/100      | 350/200            |
| Frequency range (Hz)   | DC - 5000      | DC - 5000  | DC - 3000    | DC - 4000          |
| Max. displacement (mm) Pk - Pk                                 | 13             | 13         | 9            | 10                 |
| Max. velocity (m/s)  | 1.5            | 1.5        | 1.3          | 1.3                |
| Suspension stiffness (N/mm)                                    | 8              | 8          | 70           | 70                 |
| Effective moving mass ±5% (kg)                                 | 0.23           | 0.23       | 0.5          | 0.55               |
| Main resonance frequency (Hz) (free-swinging)                  | >2680          | >2680      | >4000        | >2700              |
| Total shaker mass (kg)   | 12             | 12         | 18           | 27                 |
| Coupling (Thread ø)  | M6             | M6         | M8           | M8                 |
| Max. power consumption at 230 V (kVA)<br>Amplifier/Blower      | 0.08/-         | 0.35/0.46  | 0.35/-       | 0.9 (incl. blower) |

| System   | TV 51140-M | TV 5220-M          | TV 50350-M         |
|--|------------|--------------------|--------------------|
| Shaker   | S 51140-M  | S 5220-M           | S 50350-M          |
| Amplifier  | BAA 1000   | BAA 1000-ET        | A 1 02 11 021 T SV |
| Blower   | TB 0140    | TB 0140            | TB 0310            |
| Rated peak force (N) Sine <sub>pk</sub> / Random <sub>RMS</sub>  | 400/311    | 1000/650           | 2700/2000          |
| Frequency range (Hz)   | DC - 5000  | 1 - 5000           | 1 - 3000           |
| Max. displacement (mm) Pk - Pk                                   | 20         | 45                 | 45                 |
| Max. velocity (m/s)  | 1.5        | 1.5                | 1.5                |
| Suspension stiffness (N/mm)                                      | 5          | electr. adjustable | electr. adjustable |
| Effective moving mass ±5% (kg)                                   | 0.4        | 1.45               | 2.3                |
| Main resonance frequency (Hz) (free-swinging)                    | >2450      | >4000              | >3000              |
| Total shaker mass (kg)   | 18         | 122                | 280                |
| Coupling (Thread ø)  | M6         | M8                 | M8                 |
| Max. power consumption at 230/400V (kVA) Amplifier/Blower (+FPS) | 2.7/1.4    | 2.7/2.5            | 17 (complete)      |

General data - For detailed technical information see product data sheets (Download at https://www.tira-gmbh.de/en/tira-gmbh/downloads/vibration-test-systems/vibration-test-systems/)

### Modal-Vibration Test Systems from 4 kN to 15 kN

Especially for modal excitation of big structures or structures with high mass TIRA offers a range of modal systems from  $4\ kN$  up to  $15\ kN$ .

These shakers are characterized by **high cross axial stiffness** and permit a max. displacement of up to 100 mm (pk-pk) due to **TMC control**.

**TMC** is an electronic armature position control system for precisely coupling the modal shaker to the specimen. The armature datum level adjustment allows the operator to offset the nominal position of the armature in relation to the body. The axial stiffness can also be adjusted electronically.

A standard feature on all modal shakers is a trunnion mount. This allows a great variety of coupling options.



Modal shaker S 55240-M/LSS

| System  | TV 55240-M/LSS     | TV 56280-M/LSS     | TV 57315-M/LSS  |
|---|--------------------|--------------------|-----------------|
| Shaker  | S 55240-M/LSS      | S 56280-M/LSS      | S 57315-M/LSS   |
| Amplifier   | A 1 02 11 021 T SV | A 1 02 11 021 T SV | A 3 01 11 063 T |
| Blower  | TB 0310            | TB 9 FUK           | TB 120 FUK      |
| Rated peak force (N) Sine <sub>pk</sub> / Random <sub>RMS</sub> | 4000/3400          | 8000/6000          | 15000/11000     |
| Frequency range (Hz)  | 1 - 2000           | 1 - 2000           | 1 - 2000        |
| Max. displacement (mm) Pk - Pk                                  | 100                | 100                | 100             |
| Max. velocity (m/s)   | 2.0                | 2.0                | 2.0             |
| Effective moving mass ±5% (kg)                                  | 11.0               | 12.0               | 18.0            |
| Main resonance frequency (Hz) (free-swinging)                   | >2500              | >2500              | >2500           |
| Total shaker mass (kg)  | 800                | 850                | 1200            |
| Coupling (Thread ø)   | M10                | M10                | M10             |
| Max. power consumption at 400 V (kVA) incl. blower              | 17                 | 17                 | 29              |

General data - For detailed technical information see product data sheets (Download at https://www.tira-gmbh.de/en/tira-gmbh/downloads/vibration-test-systems/)

# Special Modal-Vibration Test Systems 100 N to 400 N

TIRA offers a new series of special modal systems for **mobile use**. The MOSP models distinguish themselves by an **extended displacement** of 25.4 mm. The low mass by using rare-earth magnets, the through-hole in the center of the armature for attaching **tension-wire stingers** besides push/pull stingers and for accomplishing a variable adjustment of the distance to the test structure, are additional features of this series.

These shakers are characterized by a **high cross axial stiffness**.

A standard feature on all modal shakers is a trunnion mount. This allows a great variety of coupling options.

| System   | TV 51110-MOSP  | TV 51120-MOSP | TV 51140-MOSP |
|--|----------------|---------------|---------------|
| Shaker   | S 51110-MOSP   | S 51120-MOSP  | S 51140-MOSP  |
| Amplifier  | BAA 120/DA 200 | BAA 500       | BAA 1000      |
| Blower   |                | TB 0080       | TB 0140       |
| Rated peak force (N) Sine <sub>pk</sub> /Random <sub>RMS</sub> | 100/70         | 200/140       | 400/280       |
| Frequency range (Hz)   | DC - 5000      | DC - 5000     | DC - 5000     |
| Max. displacement (mm) Pk - Pk                                 | 25.4           | 25.4          | 25.4          |
| Max. velocity (m/s)  | 1.5            | 1.5           | 1.5           |
| Suspension stiffness (N/mm)                                    | 4              | 4             | 4             |
| Effective moving mass ±5% (kg)                                 | 0.23           | 0.23          | 0.4           |
| Main resonance frequency (Hz) (free-swinging)                  | >6000          | >6000         | 4000          |
| Total shaker mass (kg)   | 21             | 21            | 21            |
| Coupling (Thread ø)  | M6             | M6            | M6            |
| Max. power consumpt. at 230 V (kVA)<br>Amplifier/Blower        | 0.08/-         | 0.35/0.46     | 2.7/1.4       |

General data - For detailed technical information see product data sheets (Download at https://www.tira-gmbh.de/en/tira-gmbh/downloads/vibration-test-systems/vibration-test-systems/)



Modal shakers S 51110-MOSP, S 51120-MOSP, S 51140-MOSP

# **Stinger - Push/Pull**

A stinger consists of a thin and flexible steel rod with fixation device on each end. The stinger transfers forces in axial direction and is flexible in lateral direction to minimize lateral forces to the structure. Lateral forces are not measured by uni-axial force pickups and add unwanted random signals to the measuring process, therefore the reduction of these forces is important. Avoiding these lateral forces increases the accuracy of measurement.


The stinger is also useful for isolating the moving armature from the test structure, reducing unwanted shock forces. Additionally it helps to avoid damages to the armature and the structure by unwanted excitations.

TIRA offers a variety of stinger models, collet chucks and adapter for different types of application.

Modal adapters enable the utilisation of normal vibration exciters for modal applications.

| Push/Pull Stinger |   |  |
|-------------------|---|--|
| Designation       | Description   |  |
| TR 35833          | Push/Pull Stinger 2,5 x 200 mm (Adapter thread 10-32 UNF)                         |  |
| TR 36154          | Push/Pull Stinger 3,0 x 200 mm (Adapter thread 10-32 UNF)                         |  |
| TR 36156          | Push/Pull Stinger 2,0 x 500 mm with collet chuck M6<br>(Adapter thread 10-32 UNF) |  |
| TR 35843          | Push/Pull Stinger 2,5 x 500 mm with collet chuck M6<br>(Adapter thread 10-32 UNF) |  |
| TR 36155          | Push/Pull Stinger 3,0 x 500 mm with collet chuck M6<br>(Adapter thread 10-32 UNF) |  |

| Collet chucks (separate) |  |
|--------------------------|--|
| Designation              | Description  |
| TR 36231                 | Collet chuck M6 forTR 36156 2,0 mm (Adapter thread 10-32 UNF)  |
| TR 36232                 | Collet chuck M6 for TR 35843 2,5 mm (Adapter thread 10-32 UNF) |
| TR 36233                 | Collet chuck M6 forTR 36155 3,0 mm (Adapter thread 10-32 UNF)  |



Push/Pull StingerTR 36154 (3,0 x 200 mm), AdapterTR 36235 (10-32 UNF - M8), AdapterTR 36237 (10-32 UNF - M4), Collet chuckTR 36232

| Adapter              |   |  |
|----------------------|---|--|
| Designation          | Description   |  |
| TR 36235             | Adapter 10-32 UNF - M8  |  |
| TR 36234             | Adapter 10-32 UNF - M6  |  |
| TR 36237             | Adapter 10-32 UNF - M4  |  |
| TR 36238             | Adapter M5 - M4   |  |
| TR 36239             | Adapter M6 - M4   |  |
| Modal adapter 60-M6  | Modal adapter - Internal thread M6 for mounting on armature ø60 mm  |  |
| Modal adapter 80-M8  | Modal adapter - Internal thread M8 for mounting on armature ø80 mm  |  |
| Modal adapter 120-M8 | Modal adapter - Internal thread M8 for mounting on armature ø120 mm |  |

# TIRA company view and location



